



model 7433FP

Freeze Protected Wall Mount Eyewash

FEATURES & BENEFITS

QUALITY CONTROL

Eyewash and valve assembly is pre-built and fully water and pressure tested to ensure no leaks and proper function for reduced installation time and added peace of mind. Unit also ships with pre-assembled cast-aluminum wall bracket to assist with the installation process.

BOWL

The 11" (27.9 cm) round stainless steel receptor is supplied with a No. 2L bright finish on its exterior

VALVES

Valve is designed so the full flow of fluid remains on with a simple push of a stainless steel flag. Unit also comes equipped with a stainless steel ball and stem to provide added protection against corrosion and breakage. Self-draining valve assembly is designed for installation behind the mounting wall with a maximum wall thickness of 12" (30.5 cm), in a non-freezing environment, so the unit maintains full emergency capability in freezing conditions.

MOUNTING

Wall-mounted design makes for a space efficient piece of emergency equipment with numerous installation possibilities.

FLOW CONTROLS

ABS designed plastic anti-surge Soft-Flo heads feature built-in 1.2 gpm (4.54 L) self-regulating flow controls keeping a continuous flow of water throughout the cleansing process. Unit is also equipped with green polyethylene plastic dust covers that release with water pressure to maintain an optimal functioning product.



SPECIFICATIONS

Model 7433FP freeze protected wall-mounted eyewash shall include a stainless steel 11" (27.9 cm) round bowl, stainless steel eyewash yoke assembly with Soft-Flo ABS plastic eyewash anti-surge heads with integral flow controls and dust covers, self-draining valve, and brass stay-open ball valve equipped with stainless steel ball and stem, and stem extension. Unit to be used with a maximum wall thickness of 12" (30.5 cm) and shall include chromate protective cast-aluminum wall bracket, universal sign, 1/2" NPT inlet, and 1-1/4" NPT outlet.

OPTIONS

- ❑ Test Tag: SP170 is a green waterproof test card with space for date and initials of inspector. Used to record weekly testing of emergency equipment.
- ❑ Thermostatic Mixing Valve: Model 9201EW AXION® Emergency Tempering Valve thermostatically mixes hot and cold water to provide a safe fluid supply for a single emergency eye/face wash, with a flow rate of 10 gpm (38.8 L).
- ❑ Instantaneous Water Heater: Model TWBS.EW.H, prepackaged instantaneous electrical water heater, 480 VAC/3 phase/20 kW, fully engineered and tested system with fail-safe features to produce up to 6 gpm (22.7 L) tempered water for eye washes.
- ❑ Thermostatic Mixing Valve: Model TWBS.EWE Lead-free AXION® Emergency Tempering Valve thermostatically mixes hot and cold water to provide a safe fluid supply for emergency eyewash equipment, with a flow rate of 12 gpm (45.4 L).

For more information, visit www.hawsc.com or call (888) 640-4297.


APPLICATIONS

Where the body of any person may be exposed to injurious or corrosive materials, suitable facilities for quick drenching and cleansing of the body shall be provided within the work area for immediate emergency use. Emergency deluge showers shall be in unobstructed and accessible locations that require no more than 10 seconds for the injured person to reach. Model 7433FP is certified by CSA to meet the ANSI Z358.1 Standard for Emergency Eyewash and Shower Equipment.



For more information about any Haws product please contact Modern Plant. Our team of experts are on call to answer all your questions and provide you with any advice.

Web: www.safetyshowerstations.ie | Email: sales@modernplant.ie | Tel: 01 461 4300



- NOTES:
1. TO COMPLY WITH ANSI Z358.1-2014 FOR EMERGENCY EYEWASH OR EYE/FACE WASH:
EYEWASH OR EYE/FACE WASH SHALL BE POSITIONED SUCH THAT FLUSHING FLUID FLOW PATTERN IS NOT LESS THAN 33"
(838 mm) AND NO GREATER THAN 53" (1346 mm) FROM SURFACE ON WHICH USER STANDS, AND 6.0" (153 mm) MINIMUM FROM
WALL OR NEAREST OBSTRUCTION.
 2. HEIGHT IS DETERMINED BY WATER FLOW PATTERN HEIGHT SHOWN, WHICH IN TURN, IS DEPENDENT ON IN-LINE SUPPLY
PRESSURE.
 3. VALVE IS SELF-DRAINING. THIS PERMITS STANDING WATER TO DRAIN AFTER EACH USE PREVENTING FREEZE-UPS. PROPER
PROVISIONS MUST BE MADE FOR DRAINAGE.
 4. WHEN INSTALLING THIS UNIT, LOCAL , STATE, OR FEDERAL CODES SHOULD BE ADHERED TO FOR INSTALLATION DIMENSIONS
(LOCATIONS), WASTE AND SUPPLY REQUIREMENTS OTHER THAN SHOWN.
 5. DIMENSIONS MAY VARY BY ± 1/2 [13].



1455 KLEPPE LANE
SPARKS, NEVADA 89431
(775) 359-4712 FAX (775) 359-7424
E-MAIL: HAWS@HAWS.CO.COM
WEBSITE: WWW.HAWS.CO.COM

ECN NO. REVISED PER BY:	MODEL(S)	PART NUMBER
ECN: 5175 VWC	7433FP EYEWASH	0002080048.D
DRAWN: TRF	DATE: 05/16/91	REVISION
APPROVED: FV	DATE: 11/23/17	17
SCALE: 1:1	DRAWING TYPE: INSTALLATION	SHEET 1 OF 1